



888-231-1463 ext. 1 contactus@USAirPurifiers.com USAirPurifiers.com



| Specifications | |
|----------------|------------------------------|
| Dimensions | 20" W x 15" H x 44" L |
| Weight | 95-135 lbs |
| Power | 115V/1/60 |
| Amps | 3.8 |
| Wiring | 3 Prong With 10 Feet of Cord |
| CFM - Maximum | 1100 |
| Motor | 1/4 HP PSC |
| Cabinet | 16 Gauge Steel |
| Finish | Gray Powder Coat |
| Speed Control | Variable Controller |
| Air Flow | Straight Through |
| Decibals | 55 dBA at 5' |
| Warranty | 1 Year*, Excluding Filters |

| Warranty | 1 Year*, Excluding Filters |
|-------------------|---|
| Part # | Filtration |
| BSE-AIRPRO | 20 x 15 x 1, Washable Foam Pre Filter 20 x 15 x 24, 95% Bag Filter |
| BSE-AIRPRO-HEPA | 20 x 15 x 1, Washable Foam Pre Filter 20 x 15 x 12, 95% Bag Filter 20 x 15, 99.97% HEPA Filter |
| BSE-AIRPRO-CARBON | 20 x 15 x 1, Washable Foam Pre Filter 20 x 15 x 12, 95% Bag Filter 20 x 15 18 lb. Charcoal Canister |
| Part # | Options |
| BSE-MAG | Magnehelic Pressure Gauge 0-2" W.C. |
| BSE-WALLKIT | (2) Wall Mounting Brackets |
| BSE-CEILINGKIT | Hanging Kit (chain, eye bolts, and snap links) |
| BSE-IONIZER | Needlepoint Bipolar Ionization |

-Made in the USA

- 2 to 3 week lead times
- -Optional Needlepoint Bipolar Ionization has a 99.4% reduction rate against airborne COVID-19 surrogate virus, in 3rd party testing
- -Minimal installation & maintenance

APPLICATIONS: Provides efficient removal of irritating contaminants such as smoke, chemical fumes, mist, or dust.

METHOD OF OPERATION: Dirty air enters one side of the collector and is trapped in the filters and clean air is exhausted.

INSTALLATION: Suspend from the ceiling with chains/threaded rod or hang on the wall with brackets.

KEY BENEFITS

- Avoid health and safety hazards that cause respiratory ailments.
- Reduce make-up air requirements by cleaning and re-circulating air versus exhausting outside.
- Reduce housekeeping by filtration with airborne particles that settle on equipment.
- · Lower in cost for the amount of cfm.
- Assists meeting OSHA standards (based upon filtration and design considerations).

SIZING EXAMPLE: A company performs light soldering at several work stations in a room. The smoke irritates employees in the room. The room is 40' x 30' x 12' tall = 14,400 cubic feet.

14,000 x "air changes per hour needed." Use 6 for light dust/fumes/smoke, 8 for moderate, and 10 for heavy. 14,000 x 8 (moderate) = 115,200.

115,200 divided by 60 minutes per hour = 1,920 cfm required for all the air in the room to cycle through the filters 8 times an hour. The AIRPRO is rated for 1,100 cfm, so 1,920 divided by 1,100 = 1.75 units required.

For this application we would recommend (2) AIRPRO-HEPA's staggered in the room. The HEPA filter option is best for smoke. However, (2) AIRPRO-CARBON's could be used if smell is more of an issue than the smoke.

Needlepoint Bipolar Ionization would be an effective addition for either issue as well.



IONIZATION (NPBI)

BSE's ambient air cleaners with ionization are designed for use anywhere that fine airborne contaminants, odors or pathogens are a concern. The multiple stages of filters in our units provide "active" filtration of the dirty air passing through them, while the ionizer projects ions via the exhaust air to provide "passive" air filtration outside of the unit.

NPBI – The patented Needlepoint Bipolar Ionization (NPBI) technology utilized in our units uses an electronic charge to create a plasma field filled with a high concentration of + and –ions. As these ions travel with the air stream they attach to particles, pathogens and gases. The ions help to agglomerate sub-micron particles. This makes them filterable, kill pathogens by robbing them of life-sustaining hydrogen, and breaks down harmful VOCs into harmless compounds like oxygen, carbon dioxide, nitrogen, and water vapor. This process maximizes the overall effectiveness of the units to safely clean the air inside your building. These ionizers are all UL2998 & UL867 approved, meaning no harmful ozone is produced.

FILTERS

Pre-Filters – A 1" washable foam pre-filter is provided. These are used to economically capture larger particles in the air while keeping the cost of the filter to a minimum.

Bag Filters – These are high quality, micro-glass, multi-pocket, MERV 15 bag filters which handle the largest share of the particulate filtration process.

Charcoal (optional) – The unit can be equipped with an 18 lb. charcoal cannister. This allows for active adsorption of gaseous air contaminants (VOC's) by attraction to, and bonding of, the molecules to the surface of the carbon. Adsorption is a critical component for reducing VOC's and odors in the air.

HEPA Filters (optional) – Available in our AIR PRO series units, HEPA filters are installed as a 3rd stage of filtration after the above bag filters. These commercial/industrial grade filters are rated at 99.97% efficiency based on a .30 micron particle. HEPA filters are suitable anytime sub-micron particles are an issue in your environment.

All filters are disposable and easy to access within the unit, allowing for quick and simple maintenance.