



Isolation, Particle Abatement

UV option for Antigen and Pathogen Sterilization

The Airpura I-600 Specially designed for use in healthcare clinics and institutions.

Large HEPA filter Traps airborne droplets.

Optional UV germicidal lamp Sterilizes antigens and pathogens.

Optional HI-C carbon weave Adsorbs odors and airborne chemicals and gases.


Effective for up to 2000 square feet Recycles the air approximately every 30 minutes.

Optional negative air accessories available Enables you to quickly create an isolation area.

Solid easy to move, lockable casters Weighs less than 30 lbs. Moves easily and casters can be locked in place.

High Quality HEPA Filter

- Over 100 square feet of filtration surface with 3" deep folds.
- The Hepa is warm rolled to avoid cracking at the folds and avoid leakage.
- Spacers keep the folds open and make sure that all the surface area is filtering.





The Airpura I-600

Available in White / Black / Cream The Airpura Limited Warranty 2 years parts 5 years labor

Filter Life

Hepa filters typically last 5 years in regular use.

Pre-filters can be vacuumed from the exterior of the unit and should be changed preferably every 3 months depending on use.

HI-C carbon weave (optional) should be changed every 4-6 months depending on use.

Safe effective air filtration with negative air option





Technical **Specifications**

Particle removal

Over 100 sq ft true HEPA (Measured only 1 side) 10 pleats per inch Pleats warm rolled with separators

Odor and chemical Suppression (Optional) 306 sq" HI-C carbon weave

Air Flow 560 cfm More cfm than any other home unit available

Pre-filter 570 sq in x 1in deep

Housing Powder coat steel

Size 23" x 15"

Weight 35 lbs total

Voltage Options

115 or 220 volts

Watts 120 on high 40 on low

Sound Level 28.1 db on low (at 6 feet) 62.3 db on high (560 cfm) (Room level 25.1 db)


ETL Certified Conforms to CSA C22.2 no 113 ANSI / UL 507

Your Airpura Dealer

Unique Features

- Pressure seal Airpura's unique pressure seal on the filter chamber ensures that all of the dirty air passes through the filters. Other systems allow leakage and do not achieve the 99.97% HEPA filtration rating
- Felt gaskets seal the filter chamber. Maximize filtration with no rubber off-gassing found with other filters
- All metal housing ensures no plastic vapors are emitted
- Backward curved motorized impeller eliminates the vibrations and noise associated with older motor and shaft set ups
- Variable speed motor lets you choose your ideal level of filtration
- Motor out of the air flow. Most air purifiers blow the clean air over the motor and pick up fresh impurities
- Unimpeded airflow simple and direct internal airflow avoids the air turbulence, inefficiency and noise associated with more convoluted systems
- Separate electrical parts chamber prevents any off gassing from capacitors, condensers or switches,
- Perforated steel exterior offers both a softer appearance and 360 degree air intake and distribution.
- Separately changeable filters The Hepa and carbon filters can be changed separately so you only change them when appropriate and save operating costs

Filtration System



Developed by the atomic energy commission to filter radio active particles as small as 0.3 microns Also known as paratrooper carbon, it is used to protect soldiers from poisonous gases and chemical warfare

Large scale HEPA filtration protects against airborne particles